



# 12-Ton Remote C-Head Crimper, 10,000 psi, Uses U Dies, #8 AWG - 750 kcmil Copper and Aluminum, up to 3/4" Ground Rod

By Burndy  
Catalog # Y35BH



12T Remote C-Head Crimper, 10,000 psi, Uses U Dies, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod.

## Features

- Lifting eye
- 0.95" jaw opening
- Uses U style dies
- Positive die lock buttons

## Application

Crimping

## General

|                          |   |
|--------------------------|---|
| Application - For Use On | Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod |
| Crimp Force Capacity     | 12 ton  |
| Die Type                 | U Die   |
| EU RoHS Indicator        | Yes   |
| Sub Brand                | HYPRESS   |
| Tool Type                | Remote Hydraulic Crimper  |
| Trade Name               | HYPRESS™  |
| UPC                      | 781810408452  |
| UPC 12 Digit             | 7818104084522   |

## Dimensions

|                                 |                             |
|---------------------------------|-----------------------------|
| Dimension - Length Overall inch | 9.75 in                     |
| Dimensions                      | 2.62 in x 4.75 in x 9.25 in |
| Height                          | 9.25 in                     |
| Jaw Width                       | 0.95 in                     |
| Length                          | 2.62 in                     |
| Weight                          | 8 lb                        |
| Width                           | 4.75 in                     |

## Conductor Related

|                 |   |
|-----------------|---|
| Crimping Ranges | Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only) |
|-----------------|---|

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

|                       |                  |
|-----------------------|------------------|
| Minimum Pack Quantity | 1                |
| Package Contents      | Tool, Metal Case |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_Y35BH\\_LinaArt](#)  
[Sales Drawings - SE209028-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-Y35BH-SPEC-EN | REV 5/2024