



12-Ton Remote Covered C-Head Crimper, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod

By Burndy
Catalog # Y35BH4



12T Remote Covered C-Head Crimper, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod.

Features

- Lifting eye
- 0.95" jaw opening
- Uses U style dies
- Positive die lock buttons

Application

Crimping

General

Application - For Use On	Copper, N30-N500 Navy, Flex: #8-750 kcmil; Aluminum: #8-750 kcmil; Grounding Taps: Copper #8-500 kcmil; Ground Rod: up to 3/4"
Catalog Number	Y35BH4
Crimp Force Capacity	12 ton
Die Type	U Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810408438
UPC 12 Digit	7818104084388

Dimensions

Dimensions	2.62 in x 4.75 in x 9.25 in
Height	9.25 in
Jaw Width	0.95 in
Length	2.62 in
Weight	8 lb
Width	4.75 in

Conductor Related

Crimping Ranges

Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool, Metal Case

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_Y35BH_LineArt](#)
[Sales Drawings - SE209028-01](#)
[Specifications - Y35BH4](#)



A Hubbell brand