

Compression Splice Reducer

By Burndy
Catalog # Y3634R



600 kcmil CU Long Barrel Size Reduced Down To 500 kcmil Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, BROWN Color Code, 20 or 299 Die Index.

Application

Wire Reducing Splice Adapter Insert

General

Color Code	Green
Connector Type	LONG BARREL
Die Index	22
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Sub Brand	REDUCER/ADAPTER
Temperature Rating	194
Type	Y-R, Compression
UPC	781810036822
UPC 12 Digit	7818100368222

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.69 in
Dimension - Outside Diameter inch	0.910 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	600 kcmil
Conductor - Copper Str Run Range	600 kcmil
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Str Tap	500 KCMIL
Conductor - Copper Str Tap Range	500 kcmil
Conductor - Material	COPPER
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	14400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..016040-01](#)