



Y4439R, Compression Splice Reducer, Barrel A 1000 kcmil, Barrel B 750 kcmil

By Burndy
Catalog # Y4439R



1000 kcmil CU Long Barrel Size Reduced Down To 750 kcmil Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, WHITE Color Code, 27 Die Index.

Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

General

Catalog Number	Y4439R
Color Code	White
Connector Type	LONG BARREL
Die Index	27
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810085905
UPC 12 Digit	7818100859055

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Inside Diameter inch	1.03 in
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - Outside Diameter inch	1.159 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	1000 kcmil
Conductor - Copper Str Run Range	1000 kcmil
Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Str Tap	750 KCMIL
Conductor - Copper Str Tap Range	750 kcmil
Conductor - Material	COPPER
Conductor Type	CODE
Wire Size	750 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..016040-01](#)



A Hubbell brand