

11-Ton Dieless Remote C-Head Crimper with Male Couplers

By Burndy
Catalog # [Y444SBH](#)



11T Dieless Remote C-Head Crimper, Male Couplers.

Features

- C-Head, Dieless System with Range Taking Capability
- #4 -1000 kcmil Cu & Al, #4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation
- Unique 444S Crimp Embossment
- Connections are UL Listed to UL 486A-486B on Copper and Aluminum terminals and splices. Comply with ANSI C119.4 on YDS-RL and YDS-RLNI Splices (ACSR, AAC, AAAC, ACAR). Qualified for use on YCP-L Compression Pulling Heads.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Catalog Number	Y444SBH
Crimp Force Capacity	11 ton
Die Type	Dieless
Tool Type	Remote Hydraulic Crimper

Trade Name	HYPRESS™
Type	Crimper
UPC	621945488021

Dimensions

Dimensions	3.2 in x 13.7 in x 16.9 in
Height	16.9 in
Length	3.2 in
Width	13.7 in

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50060031](#)
[Specifications - Y444SBH](#)