

11-Ton Dieless Remote C-Head Crimper with Female Couplers

By Burndy
Catalog # Y444SBHF



11T Dieless Remote C-Head Crimper, Female Couplers.

*Representative Image

Features

- C-Head, Dieless System with Range Taking Capability
- #4 -1000 kcmil Cu & Al, #4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation
- Unique 444S Crimp Embossment
- Connections are UL Listed to UL 486A-486B on Copper and Aluminum terminals and splices. Comply with ANSI C119.4 on YDS-RL and YDS-RLNI Splices (ACSR, AAC, AAAC, ACAR). Qualified for use on YCP-L Compression Pulling Heads.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Catalog Number	Y444SBHF
Crimp Force Capacity	11 ton
Die Type	Dieless
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	621945488038

Dimensions

Dimensions	3.2 in x 13.7 in x 16.9 in
Height	16.9 in
Length	3.2 in
Width	13.7 in

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50060031](#)
[Specifications - Y444SBHF](#)