



15-Ton Remote C-Head Crimper, 10000 psi, Uses S Dies

By Burndy
Catalog # [Y45](#)



15T Remote C-Head Crimper, 10000 psi, Uses S Dies.

Features

- Large jaw opening
- Quick disconnect hydraulic fitting
- C-Shaped hook style head
- Heavy duty reinforced forged steel body

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod
Crimp Force Capacity	15 ton
Die Type	S Die and U Die with PT6515 Adapter
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810625156
UPC 12 Digit	7818106251566

Dimensions

Height	0 in
Length	15.25 in
Weight	15.5 lb
Width	4.5 in

Conductor Related

Crimping Ranges

Tension Sleeves: Copper #8 sol. - 500 kcmil, Aluminum #6 sol. - 954 kcmil, ACSR #4 - 795 (26/7) kcmil; Taps: Aluminum #14 - 954 (18/1) kcmil, ACSR #6 - 795 (54/7) kcmil; Aerial Cable Connectors: Copper #6 str. - 1500 kcmil, Aluminum #4 str. - 1000 kcmil; HYGROUND® Compression Grounding: Copper #6 - 500 kcmil, 1/2" - 1" ground rods; Code Cable Terminals/Splices: Copper #8 - 1500 kcmil, Aluminum #8 - 1000 kcmil; Code Cable Taps: Copper #14 - 1000 kcmil, Aluminum #14 - 900 kcmil

Certifications And Compliance

Standards - RoHS Compliance EX Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_Y45_Lineart](#)
- [Sales Drawings - SE210372-01](#)



A proud member of the Hubbell Family.