



Y4644R, Compression Splice Reducer, Barrel A 1500 kcmil, Barrel B 1000 kcmil

By Burndy
Catalog # [Y4644R](#)



Copper Compression Reducing Adapter, 1500 kcmil - 1000 kcmil STR AWG, 3.19" Long, Tin Plated.

Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

General

Catalog Number	Y4644R
Connector Type	LONG BARREL
Die Index	31
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810219232
UPC 12 Digit	7818102192322

Dimensions

Dimension - B Length inch	3.19 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - Outside Diameter inch	1.440 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	1500 kcmil
Conductor - Copper Str Run Range	1500 kcmil
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Copper Str Tap	1000 KCMIL
Conductor - Copper Str Tap Range	1000 kcmil
Conductor - Material	COPPER
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	4625

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_Y46HYPRESS_LineArt](#)
[Sales Drawings - SD..016040-01](#)
[Specifications - Y4644R](#)