

# 15-Ton Remote Covered C-Head Crimper, 10000 psi, Uses P and U Dies with PUADP1 Adapter

By Burndy  
 Catalog # [Y46CLWSBH](#)



15T Remote Covered C-Head Crimper, 10000 psi.

\*Representative Image

## Features

- 2" jaw opening
- Used with P dies and U dies with PUADP1 adapter (sold separately)
- Positive push button die locks
- Light weight scoop style open head design with rubber cover

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46CLWSBH
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673744

UPC 12 Digit 7818106737444

## Dimensions

Length 14.68 in  
 Weight 14.5 lb

## Certifications And Compliance

Standards - RoHS Compliance UI  
 Status

## Logistics

Minimum Pack Quantity 1  
 Package Contents Tool, Nylon Carry Bag

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50024880](#)  
[Specifications - Y46CLWSBH](#)