



# 15-Ton Remote Covered C-Head Crimper, 10000 psi, Female Coupler, Uses P and U Dies with PUADP1 Adapter

By Burndy  
Catalog # Y46CLWSBHF

15T Remote Covered C-Head Crimper, 10000 psi, Female Coupler.



\*Representative Image

## Features

- 2" jaw opening
- Used with P dies and U dies with PUADP1 adapter (sold separately)
- Positive push button die locks
- Light weight scoop style open head design with rubber cover

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46CLWSBHF
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673751
UPC 12 Digit	7818106737511

## Dimensions

Length	14.68 in
Weight	14.5 lb

## Certifications And Compliance

Standards - RoHS Compliance	UI
Status	

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50024880](#)
- [Specifications - Y46CLWSBHF](#)



A Hubbell brand