



15-Ton Remote Covered C-Head Crimper, 10000 psi, Female Coupler, Uses P and U Dies with PUADP1 Adapter

By Burndy
Catalog # [Y46CLWSBHF](#)

15T Remote Covered C-Head Crimper, 10000 psi, Female Coupler.

Features

- 2" jaw opening
- Used with P dies and U dies with PUADP1 adapter (sold separately)
- Positive push button die locks
- Light weight scoop style open head design with rubber cover

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46CLWSBHF
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673751



*Representative Image

UPC 12 Digit 7818106737511

Dimensions

Length	14.68 in
Weight	14.5 lb

Certifications And Compliance

Standards - RoHS Compliance UI
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50024880](#)
- [Specifications - Y46CLWSBHF](#)