



15-Ton Remote Latch Head Crimper, 10000 psi, Female Coupler, Uses P and U Dies with PUADP1 Adapter

By Burndy
Catalog # [Y46LWBHF](#)



15T Remote Latch Head Crimper, 10000 psi, Female Coupler.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46LWBHF
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673737
UPC 12 Digit	7818106737377

Dimensions

Dimensions	14.88 in x 5.06 in x 14.88 in
Height	14.88 in
Length	14.88 in
Weight	12.4 lb
Width	5.06 in

Conductor Related

Crimping Ranges	Copper - #8 AWG Str. - 1500 kcmil; Aluminum - #8 AWG - 1250 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag
Pallet Quantity	44

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50024880](#)
- [Specifications - Y46LWBHF](#)