



15-Ton Remote C-Head Crimper, Operating Pressure 10000 psi, Uses P and U Dies with PUADP1 Adapter

By Burndy
Catalog # [Y46LWSBH](#)



15T Remote C-Head Crimper, 10000 psi.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Under Review
Sub Brand	CRIMPER - REMOTE HYDRAULIC
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810673713
UPC 12 Digit	7818106737133

Dimensions

Height	0 in
Length	14.68 in
Weight	14.5 lb
Width	2.88 in

Conductor Related

Crimping Ranges	Copper - #8 AWG Str. - 1500 kcmil; Aluminum - #8 AWG - 1250 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	UI
---------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50024880](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y46LWSBH-SPEC-EN | REV 5/2024