



## 15-Ton Remote C-Head Crimper, 10000 psi, Female Coupler.

By Burndy  
Catalog # Y46LWSBHF

15T Remote C-Head Crimper, 10000 psi, Female Coupler.



### Application

Crimping

### General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46LWSBHF
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673720
UPC 12 Digit	7818106737200

### Dimensions

Height	14.68 in
Length	14.68 in
Weight	14.5 lb

### Conductor Related

Crimping Ranges	Copper - #8 AWG Str. - 1500 kcmil; Aluminum - #8 AWG - 1250 kcmil
-----------------	---

### Certifications And Compliance

Standards - RoHS Compliance Status	UI
---------------------------------------	----

### Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50024880](#)  
[Specifications - Y46LWSBHF](#)



A Hubbell brand