



## 6-Ton 4-POINT® Dieless C-Head Remote Crimper, Range Taking.

By Burndy  
Catalog # Y4PC834MBH

6T 4-POINT® Dieless C-Head Remote Crimper.



### Features

- Dieless System
- Range taking capabilities
- C-shaped head design
- 360° head rotation

### Application

Crimping

### General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Catalog Number	Y4PC834MBH
Crimp Force Capacity	6 ton
Die Type	Dieless
Tool Type	Remote Hydraulic Crimper
Trade Name	4-POINT®
Type	Crimper
UPC	781810456538
UPC 12 Digit	7818104565388

### Dimensions

Length	13.9 in
Weight	8.35 lb
Width	5.4 in

### Conductor Related

Crimping Ranges	Copper Terminals: #8-1000 kcmil Copper Splices: #8-500 kcmil Copper Flex Terminals: #8-777.7 Flex Copper Flex Splices: #8-500 kcmil Aluminum Terminals: #8-750 kcmil Aluminum Splices: #8-350 kcmil* *1.06" barrel diameter maximum for aluminum splices due to jaw opening Aluminum HYPLUG™: #8-750 kcmil
-----------------	---

### Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_Y4PC834MBH\\_LineArt](#)
- [Sales Drawings - 10078379](#)
- [Specifications - Y4PC834MBH](#)