



60-Ton Remote Latch Head Hydraulic Crimper, Single Action Ram, 10000 psi, Uses L Dies.

By Burndy
Catalog # Y60BHU



60T Remote Latch Head Crimper, Single Action, 10000 psi.

Features

- Remote power operated
- Used with BURNDY L, wide L style dies

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices; Transmission and Distribution Connectors
Crimp Force Capacity	60 ton
Die Type	L Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810010358
UPC 12 Digit	7818100103588

Dimensions

Dimensions	11.31 in x 6.75 in x 16.62 in
Height	16.62 in
Length	11.31 in
Weight	70 lb
Width	6.75 in

Certifications and Compliance

Standards - RoHS Compliance Status EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE..086030-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y60BHU-SPEC-EN | REV 1/2024