



60-Ton Remote Latch Head Hydraulic Crimper, Single Action Ram, 10000 psi, with Stand and Case, Uses L Dies and HPS/Fargo Equivalent Dies

By Burndy
Catalog # Y60LW



60T Remote Latch Head Crimper, Single Action, 10000 psi, Stand and Case.

Features

- Remote power operated
- Used with BURNDY L, wide L style dies, and HPS/Fargo equivalent 60 ton dies
- Base stand and metal carry case (for head only) included
- Side lift handle
- Single Acting Ram With Heavy Duty Return Spring
- Fast Easy Die Changing And Secure Die Positioning With Positive Die Release Locking Pins

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices; Transmission and Distribution Connectors
Crimp Force Capacity	60 ton
Die Type	L Die
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810545218
UPC 12 Digit	7818105452188

Dimensions

Height	12.93 in
Length	0.000 in
Weight	43 lb
Width	8.06 in

Conductor Related

Crimping Ranges

Transmission and distribution connectors tension sleeves -
Copper: 1/0 STR. - 1000 kcmil, Aluminum: 1/0 STR. - 2300 kcmil, ACSR: 1/0 STR. - 2156 (84/19 STR.); Aerial - Copper: 4/0 STR. - 2500 kcmil, Aluminum: 3/0 STR. - 2500 kcmil

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Tool, Stand, Metal Case
Pallet Quantity	18

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30026179](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y60LW-SPEC-EN | REV 1/2024