



60-Ton Remote Latch Head Hydraulic Crimper, Single Action Ram, 10000 psi, No Stand.

By Burndy
Catalog # [Y60LWLS](#)

60T Remote Latch Head Crimper, Single Action, 10000 psi, No Stand.



Features

- Remote power operated
- Side lift handle
- Single acting ram with heavy duty return spring
- Fast easy die changing and secure die positioning with positive die release locking pins
- Used with BURNDY L, wide L style dies, and HPS/Fargo equivalent 60 ton dies

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices; Transmission and Distribution Connectors
Crimp Force Capacity	60 ton
Die Type	L Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810550083
UPC 12 Digit	7818105500833

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Tool, Metal Case
Pallet Quantity	18

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y60LWLS-SPEC-EN | REV 1/2024