



# 11-Ton Dieless One-Crimp Latch Head Crimper, Range Taking Capability, Self Contained Hydraulic

By Burndy  
Catalog # [Y644HSXT](#)



11T Dieless One-Crimp Latch Head Crimper, Range Taking.

## Features

- Ergonomic handle design
- Comfort grip handles
- Handle trigger drain
- 355° head rotation
- Dieless system
- Audible "Pop-Off" pressure relief valve
- Pivoting die nest

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810458358
UPC 12 Digit	7818104583588

## Dimensions

Dimensions	23.20 in x 7.04 in x 3.00 in
Height	3 in
Length	23.2 in
Weight	15 lb
Width	7.04 in

## Conductor Related

Crimping Ranges	Copper #6 - 1000 kcmil, Aluminum #6 - 750 kcmil
-----------------	---

## Certifications And Compliance

Standards - RoHS Compliance EX Status

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Plastic Case

## Product Assets

- [3D Models - Y644HSXT\\_MODEL-IGES](#)
- [3D Models - Y644HSXT\\_MODEL-PDF](#)
- [3D Models - Y644HSXT\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_Y644HSXT\\_LineArt](#)
- [Sales Drawings - 10074292](#)



A proud member of the Hubbell Family.