



12-Ton Remote C-Head Crimper, Operating Pressure 10000 psi, Uses U Dies

By Burndy
Catalog # Y750BHXT



12T Remote C-Head Crimper, 10000 psi.

Features

- 355° head rotation
- Used with U style dies
- Exposed positive die lock buttons

Application

Crimping

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810458594
UPC 12 Digit	7818104585944

Dimensions

Dimensions	12.8 in x 5.2 in x 2.9 in
Height	2.9 in
Jaw Width	1.65 in
Length	12.8 in
Weight	10.8 lb
Width	5.2 in

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10088816](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y750BHXT-SPEC-EN | REV 1/2024