



6-Ton 4-POINT® Dieless Remote Latch Head Crimper, Operating Pressure 10,000 psi, #8 AWG - 1000 kcmil CU, #8 - 750 kcmil AL

By Burndy
Catalog # Y81K2MBH

6T 4-POINT® Dieless Remote Latch Head Crimper, Guides, 10,000 psi.



Features

- Dieless System with range taking capabilities
- 360° head rotation
- Flip top design
- Unique crimping guides for improved reliability and ease of use
- Incorporates Parker-type quick connect 3/8" male coupler

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Catalog Number	Y81K2MBH
Container Type	Nylon Carry Bag
Crimp Force Capacity	6 ton
Die Type	Dieless
Tool Type	Remote Hydraulic Crimper
Trade Name	4-POINT®
Type	Crimper
UPC	621945650022
UPC 12 Digit	621945650022

Dimensions

Dimensions	12.3 in x 2.5 in x 5.4 in
Height	5.4 in
Length	12.3 in
Weight	8.5 lb
Width	2.5 in

Conductor Related

Crimping Ranges	Copper: #8 AWG -1000 kcmil; Copper Flex: #8 AWG - 777.7 kcmil; Aluminum: #8 AWG - 750 kcmil
-----------------	--

Certifications And Compliance

Buy American Compliant	No
------------------------	----

Logistics

Package Contents	Tool, Nylon Carry Bag
------------------	-----------------------

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50123581](#)
[Specifications - Y81K2MBH](#)
[Video - PATRIOT® 4-POINT® PAT81K2](#)