

## Hand Held Full Cycle Ratchet Crimper, #22 - 8 AWG, Each indenter has its own identifying mark for inspectability



By Burndy  
Catalog # Y8MRB1

Full Cycle Ratchet Crimper, #22-8 AWG, Embossment.

### Features

- Light weight
- Each indenter has unique identifying marks for inspectability
- Fully enclosed, protected ratchet mechanism does not allow the handles to be opened until full ratchet cycle is completed
- Inspection gauges available to check each groove

### Application

- Crimping

### General

Application - For Use On	#22-8 AWG Uninsulated Terminals and Splices
Catalog Number	Y8MRB1
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810031100
UPC 12 Digit	7818100311000

### Dimensions

Dimensions	10.56 in x 3.50 in x 1.04 in
Height	1.04 in
Length	10.56 in
Weight	1.21 lb
Width	3.5 in

### Conductor Related

Crimping Ranges	#22 - #8 AWG
-----------------	--------------

### Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance	EX
Status	

### Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_Y8MRB1-LineArt](#)  
[Sales Drawings - SD207164-01](#)  
[Specifications - Y8MRB1](#)