



## Compression Terminal

By Burndy  
Catalog # YA1C

1 AWG CU, One Hole, 5/16 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GREEN Color Code, 11 or 375 Die Index.



### General

EU RoHS Indicator	Yes
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated

### Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

### Electrical Ratings

Voltage Rating	35 kV
----------------	-------

### Conductor Related

Conductor - Copper Str Size Range	1 AWG
-----------------------------------	-------

### Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [3D Models - YA1C\\_MODEL-STEP](#)
- [3D Models - YA1C\\_MODEL-PDF](#)
- [3D Models - YA1C\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD..079849-03](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA1C-SPEC-EN | REV 8/2023