

YA25TC10, Compression Terminal, 1/0 AWG Cu, 1-Hole, #10 Stud, Long Barrel

By Burndy
Catalog # [YA25TC10](#)



1/0 AWG CU, One Hole, #10 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, PINK Color Code, 12 or 348 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

Application

Wire Termination

General

Catalog Number	YA25TC10
Color Code	Pink
Connector Type	LONG BARREL
Die Index	12
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810019665
UPC 12 Digit	7818100196655

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	#10
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - D inch	0.52 in
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21

Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.30 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.27 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance CM
Status
UL Listed Yes

Logistics

Carton Quantity 10
Minimum Pack Quantity 10

Product Assets

Catalogs - BURNDY Master Catalog - Section C - Compression Connections
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SD..079849-03
Specifications - YA25TC10
Video - HYDENT Compression Terminal Overview Video



A Hubbell brand