

# Compression Terminal

By Burndy  
Catalog # [YA262NT14E1](#)

2/0 AWG CU, Two Hole, 1/4 Stud Size, 1 Hole Spacing, Long Barrel, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.



## Application

Wire Termination

## General

Color Code	Black
Connector Type	LONG BARREL
Die Index	13
Feature - Barrel Style	Chamfered
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672617

## Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	91 mm
Dimension - Length Overall inch	3.59 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1-9/16 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - 50046214](#)  
[Video - HYDENT Compression Terminal Overview Video](#)

