



YA26LBOX, 2/0 AWG, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window

By Burndy
Catalog # YA26LBOX



2/0 AWG CU, One Hole, 3/8 Stud Size, Standard Barrel,
Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90°
Up to 35kV, BLACK Color Code, 13 Die Index.

Application

Wire Termination

General

Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">ChamferedSkived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810553756
UPC 12 Digit	7818105537566

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.19 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

[3D Models - YA26LBOX_MODEL-IGES](#)

[3D Models - YA26LBOX_MODEL-PDF](#)

[3D Models - YA26LBOX_MODEL-STEP](#)

[Catalogs - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - sd079848-09](#)

[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size fraction 3/8
Dimension - Stud Size inch 3/8
Dimension - Z inch 0.42 in
Physical Attribute - Tongue Straight
Angle



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA26LBOX-SPEC-EN | REV 8/2023