

YA26LNT875MMSL, Compression Terminal, 2/0, 1-Hole, 8.7mm Stud, Narrow Tongue

By Burndy

Catalog # YA26LNT875MMSL



HYLUG™ Copper Compression Terminal; Narrow Tongue; 1-Hole; Standard Barrel; Accommodates: 2/0; Stud Size: 8.75mm.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

| | |
|--------------------------------------|----------------------|
| Catalog Number | YA26LNT875MMSL |
| Color Code | Black |
| Connector Type | STANDARD BARREL |
| Die Index | 13 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| UPC | 781810463635 |

Dimensions

| | |
|----------------------------------|----------|
| Dimension - B Length fraction | 15/16 in |
| Dimension - B Length inch | 0.94 in |
| Dimension - Bolt Size fraction | 5/16 |
| Dimension - Bolt Size inch | 0.3125 |
| Dimension - Hole Size fraction | 5/16 |
| Dimension - Hole Size inch | 0.38 |
| Dimension - Hole Size mm | 10 mm |
| Dimension - Inside Diameter inch | 0.44 in |

| | |
|-----------------------------------|----------|
| Dimension - L Length Overall mm | 67 mm |
| Dimension - Length Overall inch | 2.62 in |
| Dimension - N inch | 0.33 in |
| Dimension - Outside Diameter inch | 0.56 in |
| Dimension - Pad Width inch | 0.83 in |
| Dimension - Stud Size fraction | 5/16 |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|--|---------------|
| Conductor - Copper Str Navy Size | 125 (61) Navy |
| Conductor - Copper Str Navy Size Range | 125 (61) Navy |
| Conductor - Copper Str Size | 2/0 AWG |
| Conductor - Copper Str Size Range | 2/0 AWG |
| Conductor - Material | COPPER |
| Conductor Size | 2/0 AWG |
| Conductor Type | CODE |

Certifications And Compliance

| | |
|------------------------------------|--------------|
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 1 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand