

YA27L2G1, Compression Terminal

By Burndy
Catalog # [YA27L2G1](#)



COPPER COMPRESSION TERMINAL.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA27L2G1
Color Code	Orange
Connector Type	STANDARD BARREL
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810461143
UPC 12 Digit	7818104611433

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.58 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27

Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.04 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Thread Size	1/4 in
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Navy Size Range	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD079848](#)
[Specifications - YA27L2G1](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YA27L2G1-SPEC-EN | REV 1/2025