



YA27LBOX, 3/0 AWG, CU, 1 Hole, 1/2 Stud, Standard Barrel, Inspection Window

By Burndy
Catalog # [YA27LBOX](#)



3/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel,
Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90°
Up to 35kV, ORANGE Color Code, 14 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA27LBOX
Color Code	Orange
Connector Type	STANDARD BARREL
Die Index	14
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810553800
UPC 12 Digit	7818105538000

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.54 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.13 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

[3D Models - YA27LBOX_MODEL-IGES](#)
[3D Models - YA27LBOX_MODEL-STEP](#)
[3D Models - YA27LBOX_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd079848-10](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA27LBOX-SPEC-EN | REV 8/2024