


# YA2890, Compression Terminal, 4/0 AWG, 1-Hole, 1/2" Stud, Long Barrel, 90 Degree

By Burndy  
Catalog # YA2890



Copper Compression Lug, 1 Hole w/o Inspection Window, 4/0 AWG, 1/2" Stud, Long Barrel, Tin Plated.

## Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

## Application

Wire Termination

## General

Catalog Number	YA2890
Color Code	Purple
Connector Type	LONG BARREL
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810179741
UPC 12 Digit	7818101797411

## Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm

Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.54 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	1/2
Dimension - Thread Size	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - se209241-14](#)  
[Specifications - YA2890](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YA2890-SPEC-EN | REV 10/2024