

Compression Terminal

By Burndy
Catalog # [YA28L2TC14E1](#)

4/0 AWG CU, Two Hole, 1/4 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Purple Color Code, 15 Die Index.



Application

Wire Termination

General

Color Code	Purple
Connector Type	STANDARD BARREL
Die Index	15
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810197240
UPC 12 Digit	7818101972400

Dimensions

Bolt Size	1/4 in
Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.03 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Thread Size	1/4 in
Dimension - Z inch	0.33 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD..035209-08](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z inch	0.55 in
Length	3.03 in
Outside Diameter	0.69 in
Physical Attribute - Tongue Angle	Straight



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA28L2TC14E1-SPEC-EN | REV 8/2023