

YA28L2TC14E2, Compression Terminal, 4/0 AWG Cu, 2-Hole, 1/4" Stud, 3/4" Spacing, Standard Barrel

By Burndy
Catalog # [YA28L2TC14E2](#)



4/0 AWG CU, Two Hole, 1/4 Stud Size, 3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Purple Color Code, 15 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA28L2TC14E2
Color Code	Purple
Connector Type	STANDARD BARREL
Die Index	15
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018248
UPC 12 Digit	7818100182488

Dimensions

Bolt Size	1/4 in
Dimension - B Length fraction	7/8 in

Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.78 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Thread Size	1/4 in
Dimension - Z (inch)	0.33 in
Length	2.78 in
Outside Diameter	0.69 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Certified Listed	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..035209-08](#)
[Specifications - YA28L2TC14E2](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YA28L2TC14E2-SPEC-EN | REV 1/2025