

YA29LNK, Compression Terminal, 250 kcmil Code, 250 Navy, 1-Hole, 1/2" Stud, Standard Barrel, Nickel Plated



By Burndy
Catalog # [YA29LNK](#)

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, 250 kcmil Code, 250 Navy, 600V - 35kV, 1/2" Stud, Standard Barrel, Nickel Plated.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA29LNK
Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	16
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Nickel Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810289167
UPC 12 Digit	7818102891677

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5

Dimension - D inch	1.08 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.67 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.11 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd079848-11](#)
- [Specifications - YA29LNK](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand