

## YA29TC38, Compression Terminal, 250 kcmil, 250 Navy, 1-Hole, 3/8" Stud, Long Barrel

By Burndy  
Catalog # [YA29TC38](#)



Copper Tubing Hylug, 250 kcmil, 250 Navy, 3/8 IN Bolt, 16 Index.

### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

### Application

Wire Termination

### General

Catalog Number	YA29TC38
Color Code	Yellow
Connector Type	LONG BARREL
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810145470
UPC 12 Digit	7818101454700

### Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm

Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.01 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	10
-----------------	----

Minimum Pack Quantity 10

**Product Assets**

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - sd079849-05](#)

[Specifications - YA29TC38](#)

[Video - HYDENT Compression Terminal Overview Video](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YA29TC38-SPEC-EN | REV 10/2024