



YA2C2N, 2 AWG, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Long Barrel

By Burndy
Catalog # [YA2C2N](#)

2 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.



Application

Wire Termination

General

Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810500866
UPC 12 Digit	7818105008666

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.02 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.64 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/2

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

[3D Models - YA2C2N_MODEL-PDF](#)
[3D Models - YA2C2N_MODEL-IGES](#)
[3D Models - YA2C2N_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SD..031189-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 1/2
Dimension - Z (inch) 0.64 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YA2C2N-SPEC-EN | REV 5/2024