

Compression Terminal

By Burndy
Catalog # YA2CL4

Cu Comp Terminal Code Cond, BvI Entry, 1 Hole
W/InspWindow, #2 AWG Str Code, 60 Navy, 600 V-35 kV, 3/8"
Stud, Standard Barrel, Tin Plated, Brown, 10 Index.



Application

Wire Termination

General

Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810099520

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.61 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	46400

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SD079848](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z inch 0.42 in
Physical Attribute - Tongue Straight
Angle



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA2CL4-SPEC-EN | REV 8/2023