

YA30L90, Compression Terminal, 300 kcmil Cu, 1-Hole, 1/2" Stud, Standard Barrel, 90 Degree

By Burndy

Catalog # [YA30L90](#)



Cu code conductor standard barrel, Single hole W/ insp window, 300kcmil, 1/2" stud, Tin plated, White, 17 or 298 index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA30L90
Color Code	White
Connector Type	STANDARD BARREL
Die Index	17
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810237670

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	1.08 in
Dimension - Height inch	1.89 in
Dimension - Hole Size mm	13 mm

Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.61 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	300 (91) Navy
Conductor - Copper Str Navy Size Range	300 (91) Navy
Conductor - Copper Str Size Range	300 KCMIL
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	COPPER
Conductor Size	300 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed Yes

Logistics

Carton Quantity 50
Minimum Pack Quantity 1
Pallet Quantity 12000

Product Assets

[3D Models - YA30L90_MODEL-IGES](#)
[3D Models - YA30L90_MODEL-STEP](#)
[3D Models - YA30L90_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..209240-22](#)
[Specifications - YA30L90](#)
[Video - HYDENT Compression Terminal Overview Video](#)

