

Compression Terminal

By Burndy
Catalog # YA30LTC58FX

250 kcmil, G,H CU, One Hole, 5/8 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, 16 Die Index.



Application

Wire Termination

General

Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810034521
UPC 12 Digit	7818100345211

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.94 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1-1/16 in
Dimension - Stud Size fraction	5/8
Dimension - Stud Size inch	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Size	250 KCMIL
Conductor - Copper Flex G Size Range	250 kcmil
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex H Size Range	250 kcmil
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	14800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE..208001-02](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA30LTC58FX-SPEC-EN | REV 8/2023