



YA31AY2N, Aluminum Connector

By Burndy
Catalog # [YA31AY2N](#)



HYLUG (ALUMINUM).

General

Connector Type	Terminal
Die Index	522
Feature - Barrel Style	Chamfered
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810106457
UPC 12 Digit	7818101064577

Dimensions

Dimension - B Length inch	3.56 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.86 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Pad Width inch	1.55 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	5
Pallet Quantity	4800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YA31AY2N-SPEC-EN | REV 1/2024