



# YA31L11, 350 kcmil, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window

By Burndy  
Catalog # YA31L11



350 kcmil CU, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, RED Color Code, 18 or 324 Die Index.

## Application

Wire Termination

## General

Color Code	Red
Connector Type	STANDARD BARREL
Die Index	18
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"><li>Chamfered</li><li>Skived</li></ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018040

## Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	3/8

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Navy Size	350 (91) Navy
Conductor - Copper Str Navy Size Range	350 (91) Navy
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Str Size Range	350 kcmil
Conductor - Material	COPPER
Conductor Size	350 KCMIL
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1

## Product Assets

- [3D Models - YA31L11\\_MODEL-IGES](#)
- [3D Models - YA31L11\\_MODEL-PDF](#)
- [3D Models - YA31L11\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD079848](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA31L11-SPEC-EN | REV 8/2023