

YA32L2TC38, Compression Terminal, 400 kcmil Cu, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel



By Burndy
Catalog # YA32L2TC38

400 kcmil CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 19 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

| | |
|--------------------------------------|---|
| Catalog Number | YA32L2TC38 |
| Color Code | Blue |
| Connector Type | STANDARD BARREL |
| Die Index | 19 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810018163 |
| UPC 12 Digit | 7818100181633 |

Dimensions

| | |
|-------------------------------|-----------|
| Dimension - B Length fraction | 1-3/16 in |
| Dimension - B Length inch | 1.19 in |

| | |
|-----------------------------------|----------|
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Bolt Size inch | 0.38 |
| Dimension - Hole Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 |
| Dimension - Hole Size mm | 10.4 mm |
| Dimension - L Length Overall mm | 94 mm |
| Dimension - Length Overall inch | 3.69 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 0.95 in |
| Dimension - Pad Width inch | 1.40 in |
| Dimension - Strip Length inch | 1-1/4 |
| Dimension - Stud Size fraction | 3/8 |
| Dimension - Stud Size inch | 3/8 |
| Dimension - Z (inch) | 0.42 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|-----------------------------------|----------------|
| Conductor - Copper Str Navy Size | 400 (127) Navy |
| Conductor - Copper Str Size | 400 KCMIL |
| Conductor - Copper Str Size Range | 400 kcmil |
| Conductor - Material | COPPER |
| Conductor Size | 400 KCMIL |
| Conductor Type | CODE |

Certifications And Compliance

| | |
|-------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |

| | |
|------------------------------------|--------------|
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 7500 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD035209-10](#)
- [Specifications - YA32L2TC38](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA32L2TC38-SPEC-EN | REV 10/2024