

YA32L45, Compression Terminal, 400 kcmil, 1-Hole, 5/8" Stud, Standard Barrel, 45 Degree



By Burndy
Catalog # [YA32L45](#)

Copper HYLUG™, Single Hole W/ insp window, 400 kcmil, 5/8" stud, 19 or 470 index, Blue, Tin Plated.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA32L45
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	19
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810128787

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - D inch	1.34 in
Dimension - Height inch	2.03 in
Dimension - Hole Size fraction	5/8

Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.08 in
Dimension - N inch	0.67 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size fraction	5/8
Dimension - Stud Size inch	5/8
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	400 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy
Conductor - Copper Str Size	400 KCMIL
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	COPPER
Conductor Size	400 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - Industry Standards Met UL467
Standards - RoHS Compliance Status CM
UL Listed Yes

Logistics

Carton Quantity 25
Minimum Pack Quantity 5

Pallet Quantity 7250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - se209240-26](#)
[Specifications - YA32L45](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand