



## YA32LNT38, Compression Terminal, 400 kcmil Cu, 1-Hole, 3/8" Stud, Narrow Tongue

By Burndy  
Catalog # YA32LNT38



400 kcmil CU, One Hole, 3/8 Standard Barrel, Inspection Window, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLUE Color Code, 19 Die Index.

### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

### Application

Wire Termination

### General

Catalog Number	YA32LNT38
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	19
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YA-L-NT
UPC	781810055151

### Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	1.20 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.21 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.79 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	400 KCMIL
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	COPPER
Conductor Size	400 KCMIL
Conductor Type	CODE

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	9250

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YA8CLNT8\\_LineArt](#)  
[Sales Drawings - 30003952](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YA32LNT38-SPEC-EN | REV 8/2024