



# YA34A12, Aluminum Stackable Terminal, Straight Lug

By Burndy  
Catalog # [YA34A12](#)



Aluminum Stackable Terminal- Straight Lug, 500 Kcmil, Pink,1 hole,Tin - Electro Plated.

## General

Color Code	Pink
Connector Type	Terminal
Die Index	300
Feature - Barrel Style	Chamfered
Material	Aluminum
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810130711
UPC 12 Digit	7818101307111

## Dimensions

Dimension - B Length inch	2.34 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	188 mm
Dimension - Length Overall inch	7.42 in
Dimension - Outside Diameter inch	1.32 in
Dimension - P inch	3.65 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-5/8
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	2880

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Aluminum Installation Instructions](#)  
[Sales Drawings - 210645](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YA34A12-SPEC-EN | REV 1/2024