



YA34A7N131T12E, 500 kcmil, Aluminum, 1/2 Stud, AL9CU

By Burndy

Catalog # [YA34A7N131T12E](#)

AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.



*Representative Image

Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

General

Catalog Number	YA34A7N131T12E
Color Code	Pink
Connector Type	DUAL RATED
Die Index	300
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	ALUMINUM
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YA-E
UPC	781810281376

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5

Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - Stud Size fraction	1/2
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - AL Str Size	500 KCMIL
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE
Wire Size	500 KCMIL

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	4640

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD214515-01](#)
[Specifications - YA34A7N131T12E](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA34A7N131T12E-SPEC-EN | REV 10/2024