



YA34L, 500 kcmil CU, 1 Hole, 5/8 Stud, Standard Barrel, Inspection Window

By Burndy
Catalog # [YA34L](#)



500 kcmil CU, One Hole, 5/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, BROWN Color Code, 20 or 299 Die Index.

Application

Wire Termination

General

Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	20
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">ChamferedSkived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810506202

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - D inch	1.33 in
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.37 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size fraction	5/8

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

[3D Models - YA34L_MODEL-STEP](#)
[3D Models - YA34L_MODEL-IGES](#)
[3D Models - YA34L_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SD079848](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA34L-SPEC-EN | REV 8/2023