



YA34L2NTCFX90, Compression Terminal, 373.7 kcmil, DLO 350 kcmil Flex, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Standard Barrel, 90 Degree

By Burndy
Catalog # [YA34L2NTCFX90](#)



Cu Tubing Hylug; 2 Holes with Inspection Window; 350 kcmil Flex; 600V-35kV; 1/2" stud; Standard; Compression; 0.56 in BCD; Blue.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA34L2NTCFX90
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	19
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810020180
UPC 12 Digit	7818100201800

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Height inch	2.43 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.73 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	373 KCMIL
Conductor - Copper DLO Size	373 kcmil
Range	
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper Flex G Size	350 kcmil
Range	
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex H Size	350 kcmil
Range	
Conductor - Copper Flex I Size	350 KCMIL
Conductor - Copper Flex I Size	350 kcmil
Range	
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex K Size	350 kcmil
Range	
Conductor - Copper Flex M Size	350 KCMIL
Conductor - Copper Flex M Size	350 kcmil
Size Range	
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Material	COPPER
Conductor Size	350 KCMIL
Conductor Type	FLEX
Wire Size	350 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3480

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..208119-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA34L2NTCFX90-SPEC-EN | REV 8/2024