

Compression Terminal

By Burndy
Catalog # YA34L2TC1245



COPPER COMPRESSION TERMINAL.

Application

Wire Termination

General

| | |
|--------------------------------------|---|
| Color Code | Brown |
| Connector Type | STANDARD BARREL |
| Die Index | 20 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810019474 |
| UPC 12 Digit | 7818100194744 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 1-1/4 in |
| Dimension - B Length inch | 1.27 in |
| Dimension - Bolt Hole Size inch | 0.52 in |
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - Bolt Size inch | 0.5 |
| Dimension - Height inch | 2.25 in |
| Dimension - Hole Size fraction | 1/2 |
| Dimension - Hole Size inch | 0.53 |
| Dimension - Hole Size mm | 13.5 mm |
| Dimension - L Length Overall mm | 109 mm |
| Dimension - Length Overall inch | 4.31 in |
| Dimension - N inch | 0.53 in |
| Dimension - Outside Diameter inch | 1.06 in |
| Dimension - Pad Width inch | 1.55 in |
| Dimension - Strip Length inch | 1-7/16 |
| Dimension - Stud Size fraction | 1/2 |
| Dimension - Stud Size inch | 1/2 |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - Copper Str Size | 500 KCMIL |
| Conductor - Copper Str Size Range | 500 kcmil |
| Conductor - Material | COPPER |
| Conductor Size | 500 KCMIL |
| Conductor Type | CODE |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 6 |
| Minimum Pack Quantity | 6 |
| Pallet Quantity | 2784 |

Product Assets

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - se209512-33](#)

[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z inch 0.55 in
Physical Attribute - Tongue Angle 45 Degree



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA34L2TC1245-SPEC-EN | REV 8/2023