




YA34L2TC14FX, Compression Terminal, 373.7 DLO, 2-Hole, 1/4" Stud, Standard Barrel

By Burndy
Catalog # [YA34L2TC14FX](#)



Copper Tubing Compression Terminal, 2 Holes W/insp Window, 373.7 (925/#24) DLO, 3.31 IN L, .96 IN W, 19 or 470 Index, 3/8 IN Bolt.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA34L2TC14FX
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	19
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810268537
UPC 12 Digit	7818102685377

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8

Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.31 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.32 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	373 KCMIL
Conductor - Copper DLO Size Range	373 kcmil
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper Flex G Size Range	350 kcmil
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 KCMIL
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex M Size	350 KCMIL
Conductor - Copper Flex M Size Range	350 kcmil
Conductor - Copper Str Size	350 KCMIL

Conductor - Copper Str Size Range	350 kcmil
Conductor - Material	COPPER
Conductor Size	350 KCMIL
Conductor Type	FLEX
Wire Size	350 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	5880

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE..208119-01](#)
- [Specifications - YA34L2TC14FX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand