

YA34L3790, Compression Terminal, 500 kcmil, 1-Hole, 3/8" Stud, Standard Barrel, 90 Degree

By Burndy
Catalog # [YA34L3790](#)



Copper Compression Lug, 1 Hole w/ Inspection Window, 500 kcmil, 3/8" Stud, Short Barrel, Brown, 20 or 299 index, Tin Plated, 90 Degree Bend.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA34L3790
Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	20
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810295847

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.83 in
Dimension - Height inch	2.41 in

Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.52 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1-7/18
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	6

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se209240-28](#)
- [Specifications - YA34L3790](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA34L3790-SPEC-EN | REV 10/2024